



Click [here](#) for the 3D model.

#### General Information

|                          |  |
|--------------------------|--|
| Series                   | PMR205/P405  |
| Dielectric               | Metallized Paper                                   |
| Style                    | Radial   |
| Features                 | RC Unit not approved                               |
| RoHS                     | Yes  |
| Termination              | Tinned Wire  |
| Lead                     | Wire Leads   |
| AEC-Q200                 | No   |
| Construction             | Molded   |
| Typical Component Weight | 2.7 g  |
| Miscellaneous            | Resistor Tolerance: +/-30%.<br>Resistor= 600 Ohms. |

#### Specifications

|                       |           |
|-----------------------|-----------|
| Capacitance           | 0.25 uF   |
| Tolerance             | 20%       |
| Voltage DC            | 250 VDC   |
| Voltage AC            | 125 VAC   |
| Temperature Range     | -40/+85°C |
| Rated Temperature     | 85°C      |
| Insulation Resistance | 3 GOhms   |
| Safety Class          | X2        |

#### Dimensions

|    |                 |
|----|-----------------|
| L  | 18.5mm MAX      |
| H  | 13mm MAX        |
| T  | 7.3mm MAX       |
| S  | 15.2mm +/-0.4mm |
| LL | 30mm +5mm       |
| F  | 0.8mm +/-0.05mm |

#### Packaging Specifications

|                    |           |
|--------------------|-----------|
| Packaging          | Bulk, Bag |
| Packaging Quantity | 400       |