



Click [here](#) for the 3D model.

General Information

| | |
|--------------------------|------------------|
| Series | PME271M/P276 |
| Dielectric | Metallized Paper |
| Style | Radial |
| Features | EMI Safety |
| RoHS | Yes |
| Termination | Tinned Wire |
| Lead | Wire Leads |
| Safety Class | X2 |
| Qualifications | ENEC, UL, cUL |
| AEC-Q200 | No |
| Construction | Molded |
| Typical Component Weight | 4 g |
| Miscellaneous | SRF= 4.1 MHz. |

Dimensions

| | |
|----|-----------------|
| L | 24mm MAX |
| H | 14mm MAX |
| T | 7.6mm MAX |
| S | 20.3mm +/-0.4mm |
| H0 | 18.5mm +/-0.5mm |
| F | 0.8mm NOM |

Packaging Specifications

| | |
|--------------------|------------|
| Packaging | T&R, Large |
| Packaging Quantity | 500 |

Specifications

| | |
|-----------------------|--------------|
| Capacitance | 0.1 uF |
| Capacitance Tolerance | 20% |
| Voltage DC | 630 VDC |
| Voltage AC | 275 VAC (X2) |
| Temperature Range | -40/+110°C |
| Rated Temperature | 110°C |
| Dissipation Factor | 1.3% 1kHz |
| Insulation Resistance | 12 GOhms |
| Max dV/dt | 600 V/us |