

## PME261KE6470KR30

Aliases (P561EH474K220A)

Obsolete

PME261/P561, Film, Metallized Paper, General Purpose, 0.47 uF, 10%, 400 VDC, 85°C, 25.4 mm



Click [here](#) for the 3D model.

### General Information

Series	PME261/P561
Dielectric	Metallized Paper
Style	Radial
Features	Pulse in DC and low frequency applications
RoHS	Yes
Termination	Tinned Wire
Lead	Wire Leads
AEC-Q200	No
Construction	Molded
Typical Component Weight	7.65 g
Miscellaneous	AC Operation: 70C MAX.

### Specifications

Capacitance	0.47 uF
Tolerance	10%
Voltage DC	400 VDC
Voltage AC	220 VAC
Temperature Range	-40/+100°C
Rated Temperature	85°C
Dissipation Factor	1.3% 1kHz
Insulation Resistance	8.511 GOhms
Max dV/dt	370 V/us

### Dimensions

L	30.5mm -0.5mm
H	17.3mm -0.5mm
T	10.6mm -0.5mm
S	25.4mm +/-0.4mm
LL	30mm +5mm
F	1mm +/-0.05mm

### Packaging Specifications

Packaging	Bulk, Bag
Packaging Quantity	100

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.