



Click [here](#) for the 3D model.

Dimensions	
L	30.5mm -0.5mm
H	22mm -0.5mm
T	15.3mm -0.5mm
S	25.4mm +/-0.4mm
LL	30mm +5mm
F	1mm +/-0.05mm

Packaging Specifications	
Packaging	Bulk, Bag
Packaging Quantity	75

General Information	
Series	PME261/P561
Dielectric	Metallized Paper
Style	Radial
Features	Pulse in DC and low frequency applications
RoHS	Yes
Lead	Wire Leads
AEC-Q200	No
Construction	Molded
Typical Component Weight	13.5 g
Miscellaneous	AC Operation: 70C MAX.

Specifications	
Capacitance	1 μ F
Capacitance Tolerance	10%
Voltage AC	220 VAC
Voltage DC	400 VDC
Temperature Range	-40/+100°C
Rated Temperature	85°C
Dissipation Factor	1.3% 1kHz
Insulation Resistance	12 GOhms
Max dV/dt	220 V/us