



Click [here](#) for the 3D model.

General Information

| | |
|--------------------------|--|
| Series | PME261/P561 |
| Dielectric | Metallized Paper |
| Style | Radial |
| Features | Pulse in DC and low frequency applications |
| RoHS | Yes |
| Termination | Tinned Wire |
| Lead | Wire Leads |
| AEC-Q200 | No |
| Construction | Molded |
| Typical Component Weight | 13.5 g |
| Miscellaneous | AC Operation: 70C MAX. |

Specifications

| | |
|-----------------------|-------------|
| Capacitance | 0.68 uF |
| Capacitance Tolerance | 10% |
| Voltage DC | 400 VDC |
| Voltage AC | 220 VAC |
| Temperature Range | -40/+100°C |
| Rated Temperature | 85°C |
| Dissipation Factor | 1.3% 1kHz |
| Insulation Resistance | 5.882 GOhms |
| Max dV/dt | 300 V/us |

Dimensions

| | |
|----|-----------------|
| L | 30.5mm -0.5mm |
| H | 22mm -0.5mm |
| T | 15.3mm -0.5mm |
| S | 25.4mm +/-0.4mm |
| LL | 30mm +5mm |
| F | 1mm +/-0.05mm |

Packaging Specifications

| | |
|--------------------|-----------|
| Packaging | Bulk, Bag |
| Packaging Quantity | 75 |