


PMR205AB6100M033R30

Aliases (P405QE104M125AH330)

Obsolete

PMR205/P405, Film, Metallized Paper, Resistor/Capacitor, 0.1 uF, 20%, 250 VDC, 85°C, 15.2 mm



→∐←F		Typical
	Click here for the 3D model.	Miscella
Dimensions		Specifi
L	18.5mm MAX	Capaci
Н	10.5mm MAX	Toleran
Т	5.2mm MAX	Voltage
S	15.2mm +/-0.4mm	Voltage
LL	30mm +5mm	Tempe

0.8mm +/-0.05mm

Packaging Specifications		
Packaging	Bulk, Bag	
Packaging Quantity	500	

F

General Information	
Series	PMR205/P405
Dielectric	Metallized Paper
Style	Radial
Features	RC Unit not approved
RoHS	Yes
Termination	Tinned Wire
Lead	Wire Leads
AEC-Q200	No
Construction	Molded
Typical Component Weight	1.53 g
Miscellaneous	Resistor Tolerance: +/-30%. Resistor= 33 Ohms.

Specifications	
Capacitance	0.1 uF
Tolerance	20%
Voltage DC	250 VDC
Voltage AC	125 VAC
Temperature Range	-40/+85°C
Rated Temperature	85°C
Insulation Resistance	3 GOhms
Safety Class	X2

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 12/13/2025 © 2006 - 2025 YAGEO