


## PMR205AB6250M200R30

Aliases (P405QM254M125AH201)

## Obsolete

PMR205/P405, Film, Metallized Paper, Resistor/Capacitor, 0.25 uF, 20%, 250 VDC, 85°C, 15.2 mm



Click here for the 3D model.

| Dimensions |                 |
|------------|-----------------|
| L          | 18.5mm MAX      |
| Н          | 13mm MAX        |
| Т          | 7.3mm MAX       |
| S          | 15.2mm +/-0.4mm |
| LL         | 30mm +5mm       |
| F          | 0.8mm +/-0.05mm |
|            |                 |

| Packaging Specifications |           |
|--------------------------|-----------|
| Packaging                | Bulk, Bag |
| Packaging Quantity       | 400       |

| General Information      |  |
|--------------------------|--|
| Series                   | PMR205/P405  |
| Dielectric               | Metallized Paper                                   |
| Style                    | Radial   |
| Features                 | RC Unit not approved                               |
| RoHS                     | Yes  |
| Termination              | Tinned Wire  |
| Lead                     | Wire Leads   |
| AEC-Q200                 | No   |
| Construction             | Molded   |
| Typical Component Weight | 2.7 g  |
| Miscellaneous            | Resistor Tolerance: +/-30%.<br>Resistor= 200 Ohms. |

| Specifications        |           |
|-----------------------|-----------|
| Capacitance           | 0.25 uF   |
| Tolerance             | 20%       |
| Voltage DC            | 250 VDC   |
| Voltage AC            | 125 VAC   |
| Temperature Range     | -40/+85°C |
| Rated Temperature     | 85°C      |
| Insulation Resistance | 3 GOhms   |
| Safety Class          | X2        |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute – and we specifically disclaim – any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 12/06/2025 © 2006 - 2025 YAGEO