



Click [here](#) for the 3D model.

Dimensions

D	20mm +/-0.5mm
L	37mm +/-1mm
L1	43mm MIN
LL	42mm +3/-2mm
F	0.8mm +/-0.03mm

Packaging Specifications

Sleeving	Yes
Packaging	Bulk, Bag

General Information

Series	PEG124
Dielectric	Aluminum Electrolytic
Style	Axial
Description	Long Life Axial Aluminum Electrolytic
Features	Long Life
RoHS	Yes
Lead	Wire Leads
AEC-Q200	No
Halogen Free	Yes
Typical Component Weight	20 g

Miscellaneous Life Calculation Based On Maximum Ripple Current, Please Contact KEMET For More Information.

Notes L1 is KEMETs recommendation for minimum distance between symmetrical Lead bend. Available only for Customer specific part numbers. Lead bend dimensions must be specified and confirmed per article. Dimensions D And L Include Sleeving.

Shelf Life 156 Weeks

Specifications

Capacitance	22 uF
Capacitance Tolerance	-10/+50%
Voltage DC	450 VDC
Temperature Range	-40/+105°C
Rated Temperature	105°C
Life	22000 Hrs
ESR	2100 mOhms (100Hz 20C), 800 mOhms (100kHz 20C)
Ripple Current	0.242 Amps (100Hz 105C), 2.3 Amps (5kHz 60C), 0.67 Amps (5kHz 105C)
Leakage Current	30 uA (5min 20°C)
Inductance	15 nH (ESL)