



General Information	
Series	PEH200
Dielectric	Aluminum Electrolytic
Style	Screw Terminal
Description	Screw Terminal, Aluminum Electrolytic
RoHS	Yes
Lead	Screw Terminals M5
Mounting	Through-Hole
AEC-Q200	No
Halogen Free	true
Typical Component Weight	70 g
Notes	Dimensions D And L Include Sleeving. MS (MxS) = M8x12.
Shelf Life	156 Weeks

Click [here](#) for the 3D model.

Specifications	
Capacitance	6800 uF
Capacitance Tolerance	20%
Voltage DC	40 VDC
Temperature Range	-40/+85°C
Rated Temperature	85°C
Life	10000 Hrs (Rated Voltage And Ripple Current At 85C)
ESR	33 mOhms (100Hz 20C), 25 mOhms (100kHz 20C)
Ripple Current	9.9 Amps (100Hz 85C), 27.2 Amps (10kHz 50C), 18.1 Amps (10kHz 40C)
Leakage Current	4816 uA (5min 20°C)
Inductance	12 nH (ESL)

Dimensions	
D	36.6mm +/-1mm
L	51.5mm +/-1mm
T	4.4mm NOM
S	13mm +/-0.5mm
F	8mm +/-0.5mm
DT	8mm NOM
LT	58.9mm +/-1mm

Packaging Specifications	
Sleeving	true
Packaging	Bulk, Bag
Packaging Quantity	42

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.