



Click [here](#) for the 3D model.

### Dimensions

L	13.5mm -0.5mm
H	10.5mm -0.5mm
T	5.1mm -0.5mm
S	10.2mm +0.6/-0.1mm
H0	18.5mm +/-0.5mm
F	0.6mm +/-0.05mm

### Packaging Specifications

Packaging	T&R
Packaging Quantity	600

### General Information

Series	PME261/P561
Dielectric	Metallized Paper
Style	Radial
Features	Pulse in DC and low frequency applications
RoHS	Yes
Termination	Tinned Wire
Lead	Wire Leads
AEC-Q200	No
Construction	Molded
Typical Component Weight	1.08 g
Miscellaneous	AC Operation: 70C MAX.

### Specifications

Capacitance	4700 pF
Capacitance Tolerance	10%
Voltage DC	1000 VDC
Voltage AC	500 VAC
Temperature Range	-40/+100°C
Rated Temperature	85°C
Dissipation Factor	1.3% 1kHz
Insulation Resistance	12 GOhms
Max dV/dt	2000 V/us