



Click [here](#) for the 3D model.

General Information

Series	PEG124
Dielectric	Aluminum Electrolytic
Style	Axial
Description	Long Life Axial Aluminum Electrolytic
Features	Long Life
RoHS	Yes
Lead	Wire Leads
AEC-Q200	No
Halogen Free	Yes
Typical Component Weight	24 g
Miscellaneous	Life Calculation Based On Maximum Ripple Current, Please Contact KEMET For More Information.

Notes

L1 is KEMETs recommendation for minimum distance between symmetrical Lead bend. Available only for Customer specific part numbers. Lead bend dimensions must be specified and confirmed per article. Dimensions D And L Include Sleeving.

Shelf Life 156 Weeks

Dimensions

D	20mm +/-0.5mm	Capacitance	47 uF
L	46mm +/-1mm	Tolerance	-10/+30%
L1	52mm MIN	Voltage DC	400 VDC
LL	42mm +3/-2mm	Temperature Range	-40/+105°C
F	0.8mm +/-0.03mm	Rated Temperature	105°C

Packaging Specifications

Sleeving	Yes	ESR	1200 mOhms (100Hz 20C), 530 mOhms (100kHz 20C)
Packaging	Bulk, Bag	Ripple Current	0.377 Amps (100Hz 105C), 2.4 Amps (5kHz 60C), 0.89 Amps (5kHz 105C)
		Leakage Current	56 uA (5min 20°C)
		Inductance	17 nH (ESL)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.