



Click [here](#) for the 3D model.

#### General Information

Series	PEG124
Dielectric	Aluminum Electrolytic
Style	Axial
Description	Long Life Axial Aluminum Electrolytic
Features	Long Life
RoHS	Yes
Lead	Wire Leads
AEC-Q200	No
Halogen Free	Yes
Typical Component Weight	11 g
Miscellaneous	Life Calculation Based On Maximum Ripple Current, Please Contact KEMET For More Information.

#### Notes

L1 is KEMETs recommendation for minimum distance between symmetrical Lead bend. Available only for Customer specific part numbers. Lead bend dimensions must be specified and confirmed per article. Dimensions D And L Include Sleeving.

Shelf Life 156 Weeks

#### Dimensions

D	16mm +/-0.5mm
L	37mm +/-1mm
L1	43mm MIN
LL	42mm +/-2mm
F	0.8mm +/-0.03mm

#### Specifications

Capacitance	15 uF
Tolerance	-10/+30%
Voltage DC	450 VDC
Temperature Range	-40/+105°C
Rated Temperature	105°C
Life	15000 Hrs
ESR	3600 mOhms (100Hz 20C), 1700 mOhms (100kHz 20C)
Ripple Current	0.171 Amps (100Hz 105C), 1.1 Amps (5kHz 60C), 0.41 Amps (5kHz 105C)
Leakage Current	20 uA (5min 20°C)
Inductance	12 nH (ESL)

#### Packaging Specifications

Sleeving	Yes
Packaging	Bulk, Bag

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.