



Note: '()' correspond to the letters used in the product bulletin

Click [here](#) for the 3D model.

General Information

Series	PHA227
Dielectric	Hybrid Polymer
Style	Axial
Description	Hybrid Axial Capacitors
RoHS	Yes
Lead	Wire Leads
Qualifications	AEC-Q200
AEC-Q200	Yes
Halogen Free	Yes
Typical Component Weight	13 g
Shelf Life	520 Weeks

Specifications

Capacitance	1,000 uF
Tolerance	20%
Voltage DC	63 VDC
Temperature Range	-40/+125°C
Rated Temperature	125°C
ESR	65 mOhms (100Hz 20C), 5.3 mOhms (100kHz -40C to 125C)
Ripple Current	40.6 Amps (100kHz 90C), 37.6 Amps (100kHz 105C), 25 Amps (100kHz 125C)
Leakage Current	315 uA

Dimensions

D	20.2mm +/-0.5mm
L	26.7mm +/-1mm
L1	33mm MIN
LL	40mm +/-2mm
F	1mm +/-0.03mm

Packaging Specifications

Packaging	Tray
-----------	------