



Click [here](#) for the 3D model.

Dimensions

D	66.6mm +/-1mm
L	106mm +/-1mm
T	3.8mm NOM
S	28.5mm
F	15mm +/-0.5mm
DT	15mm NOM
G	13mm NOM
LT	113mm +/-1mm
Z	13mm NOM

Packaging Specifications

Sleeving	Yes
Packaging	Bulk, Bag

General Information

Series	PEH200
Dielectric	Aluminum Electrolytic
Description	Screw Terminal, Aluminum Electrolytic
RoHS	Yes
■	Through-Hole
AEC-Q200	No
Halogen Free	Yes
Typical Component Weight	415 g
Notes	Dimensions D And L Include Sleeving. MS (MxS) = M12x16.
Shelf Life	156 Weeks

Specifications

Capacitance	4,700 uF
Capacitance Tolerance	20%
Voltage DC	250 VDC
Temperature Range	-40/+85°C
Rated Temperature	85°C
Life	15000 Hrs (Rated Voltage And Ripple Current At 85C)
ESR	29 mOhms (100Hz 20C), 18 mOhms (100kHz 20C)
Ripple Current	11.3 Amps (100Hz 85C), 38.2 Amps (10kHz 50C), 27.2 Amps (10kHz 40C)
Leakage Current	7525 uA (5min 20°C)
Inductance	16 nH (ESL)