


PHE448SB3150JR25XA

Aliases (F448BD151J2K0XLAF1)

Not for New Design

PHE448/F448, Film, Film/Foil Polypropylene, General Purpose, 150 pF, 5%, 2,000 VDC, 85°C, 7.5 mm



Click [here](#) for the 3D model.

General Information	
Series	PHE448/F448
Dielectric	Film/Foil Polypropylene
Style	Radial
Features	Pulse
RoHS	Yes
Termination	Tinned Wire
Lead	Formed To 7.5mm
AEC-Q200	No
Miscellaneous	Rthha= 87 C/W (85C), 0.2 m/s.
Notes	Not For New Design, Series Replaced by R73.

Specifications	
Capacitance	150 pF
Tolerance	5%
Voltage DC	2000 VDC, 1480 VDC (105C)
Voltage AC	700 VAC
Temperature Range	-55/+105°C
Rated Temperature	85°C
Dissipation Factor	0.03% 1kHz, 0.05% 10kHz, 0.1% 100kHz
Insulation Resistance	200 GOhms
Max dV/dt	25,000 V/us
Inductance	6 nH

Dimensions	
L	18mm -0.5mm
H	10.5mm -0.5mm
T	5.5mm -0.5mm
S	7.5mm +0.6/-0.1mm
H0	16mm +/-0.5mm
F	0.8mm +/-0.05mm
G	0.5mm NOM
Packaging Specifications	
Packaging	Ammo, 330x330x50mm, Box
Packaging Quantity	570

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.