



Note: '()' correspond to the letters used in the product bulletin

Click [here](#) for the 3D model.

General Information

Series	PHA223
Dielectric	Hybrid Polymer
Style	Axial
Description	Hybrid Axial Capacitors
RoHS	Yes
Lead	Wire Leads
Qualifications	AEC-Q200
AEC-Q200	Yes
Halogen Free	Yes
Typical Component Weight	9 g
Shelf Life	520 Weeks

Specifications

Capacitance	1,400 uF
Tolerance	20%
Voltage DC	35 VDC
Temperature Range	-40/+125°C
Rated Temperature	125°C
ESR	112 mOhms (100Hz 20C), 4.7 mOhms (100kHz -40C to 125C)
Ripple Current	39 Amps (100kHz 90C), 34 Amps (100kHz 105C), 23.4 Amps (100kHz 125C)
Leakage Current	245 uA

Dimensions

D	16.2mm +/-0.5mm
L	26.7mm +/-1mm
L1	33mm MIN
LL	40mm +/-2mm
F	1mm +/-0.03mm

Packaging Specifications

Packaging	Tray
-----------	------

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.