



Click [here](#) for the 3D model.

General Information

Series	PHBC
Style	Through-Hole
Features	Switching Power Supply Outlet, DC-DC Converter, Phase Compensation, Noise Solution
RoHS	Yes
Miscellaneous	30 (K) Temperature Rise Max.
Core	Fe-Ni

Specifications

Inductance	81 uH (0.1 MHz)
Inductance Tolerance	20%
Current	6 A
Temperature Range	-40/+125°C
DC Resistance	24.7 mOhms

Dimensions

D	30mm MAX
T	15.7mm MAX
LL	9mm +/-3mm
S	11mm NOM
Wire Size	1.2mm

Packaging Specifications

Packaging	Tray
Packaging Quantity	150
Typical Component Weight	30 g