


PHE426KK4120JR05

Aliases (F426KG122J400C, PHE426KK4120JK01R05)

Not for New Design

PHE426/F426, Film, Metallized Polypropylene, General Purpose, 1200 pF, 5%, 400 VDC, 85°C, 7.5mm



Click [here](#) for the 3D model.

Dimensions	
L	10mm MAX
H	8mm MAX
T	4mm MAX
S	7.5mm +/-0.4mm
LL	5mm NOM
F	0.6mm NOM

Packaging Specifications	
Packaging	Bulk, Bag
Packaging Quantity	1000

General Information	
Series	PHE426/F426
Dielectric	Metallized Polypropylene
Style	Radial
Features	Pulse
RoHS	Yes
Lead	Wire Leads
AEC-Q200	No
Typical Component Weight	0.456 g
Notes	Series Replaced by R75.

Specifications	
Capacitance	1200 pF
Capacitance Tolerance	5%
Voltage AC	220 VAC
Voltage DC	400 VDC, 296 VDC (105C)
Temperature Range	-55/+105°C
Rated Temperature	85°C
Dissipation Factor	0.05% 1kHz, 0.25% 100kHz
Insulation Resistance	100 GOhms
Max dV/dt	200 V/us
Inductance	6 nH

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.