


## PHE448SB4150JR17T0

Aliases (F448BJ152J2K0L)

Not for New Design

PHE448/F448, Film, Film/Foil Polypropylene, General Purpose, 1,500 pF, 5%, 2,000 VDC, 85°C, 15 mm



Click [here](#) for the 3D model.

### General Information

|                          |                                             |
|--------------------------|---------------------------------------------|
| Series                   | PHE448/F448                                 |
| Dielectric               | Film/Foil Polypropylene                     |
| Style                    | Radial                                      |
| Features                 | Pulse                                       |
| RoHS                     | Yes                                         |
| Termination              | Tinned Wire                                 |
| Lead                     | Wire Leads                                  |
| AEC-Q200                 | No                                          |
| Typical Component Weight | 2 g                                         |
| Miscellaneous            | Rthha= 82 C/W (85C), 0.2 m/s.               |
| Notes                    | Not For New Design, Series Replaced by R73. |

### Specifications

|                       |                                      |
|-----------------------|--------------------------------------|
| Capacitance           | 1,500 pF                             |
| Tolerance             | 5%                                   |
| Voltage DC            | 2000 VDC, 1480 VDC (105C)            |
| Voltage AC            | 700 VAC                              |
| Temperature Range     | -55/+105°C                           |
| Rated Temperature     | 85°C                                 |
| Dissipation Factor    | 0.03% 1kHz, 0.05% 10kHz, 0.1% 100kHz |
| Insulation Resistance | 20 GOhms                             |
| Max dV/dt             | 25,000 V/us                          |
| Inductance            | 6 nH                                 |

### Dimensions

|    |                  |
|----|------------------|
| L  | 18mm -0.5mm      |
| H  | 12.5mm -0.5mm    |
| T  | 6.5mm -0.5mm     |
| S  | 15mm +0.6/-0.1mm |
| H0 | 18.5mm +/-0.5mm  |
| F  | 0.8mm +/-0.05mm  |
| G  | 0.5mm NOM        |

### Packaging Specifications

|                    |     |
|--------------------|-----|
| Packaging          | T&R |
| Packaging Quantity | 500 |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.