

## PHE840MF7220KF15R06L2

Aliases (F840FS225K275C)

Not for New Design

Recommended Replacement Series R46 X2 310 VAC

PHE840M/F840, Film, Metallized Polypropylene, Safety, 2.2 uF, 10%, 760 VDC, 275 VAC (X2), 105°C, 27.5 mm



Click [here](#) for the 3D model.

### General Information

Series	PHE840M/F840
Dielectric	Metallized Polypropylene
Style	Radial
Features	EMI Safety
RoHS	Yes
Termination	Tinned Wire
Lead	Wire Leads
Safety Class	X2
Qualifications	ENEC, UL, cUL
AEC-Q200	No
Typical Component Weight	18.62 g
Notes	Not for new design – the replacement series is: R46 X2 310VAC.

### Dimensions

L	31.5mm MAX
H	29mm MAX
T	19mm MAX
S	27.5mm +/-0.4mm
LL	6mm NOM
F	0.8mm NOM

### Packaging Specifications

Packaging	Tray
Packaging Quantity	117

### Specifications

Capacitance	2.2 uF
Tolerance	10%
Voltage DC	760 VDC
Voltage AC	275 VAC (X2)
Temperature Range	-55/+105°C
Rated Temperature	105°C
Dissipation Factor	0.1% 1kHz, 0.8% 10kHz
Insulation Resistance	4.5454 GOhms
Max dV/dt	100 V/us

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute – and we specifically disclaim – any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.