


[Click here for the 3D model.](#)
**General Information**

Series	PHE840M/F840
Dielectric	Metallized Polypropylene
Style	Radial
Features	EMI Safety
RoHS	Yes
Termination	Tinned Wire
Lead	Wire Leads
Safety Class	X2
Qualifications	ENEC, UL, cUL
AEC-Q200	No
Typical Component Weight	33.1 g
Notes	Not for new design – the replacement series is: R46 X2 310VAC.

**Dimensions**

L	41mm MAX
H	38mm MAX
T	21mm MAX
S	37.5mm +/-0.5mm
LL	6mm NOM
F	1mm NOM

**Specifications**

Capacitance	5.6 uF
Tolerance	20%
Voltage DC	760 VDC
Voltage AC	275 VAC (X2)
Temperature Range	-55/+105°C
Rated Temperature	105°C
Dissipation Factor	0.1% 1kHz, 0.8% 10kHz
Insulation Resistance	1.7857 GOhms
Max dV/dt	100 V/us

**Packaging Specifications**

Packaging	Tray
Packaging Quantity	84

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute – and we specifically disclaim – any warranty concerning suitability for a specific customer application or use. This information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.