

## R46KN410000N2M

Aliases (46KN410000N2M)

R46 275 VAC, Film, Metallized Polypropylene, Safety, 1  $\mu$ F, 20%, 560 VDC, 275 VAC (X2), 110°C, 22.5mm



Click [here](#) for the 3D model.

Dimensions	
L	26.5mm +0.3/-0.5mm
H	18.5mm +0.1/-0.5mm
T	10mm +0.2/-0.5mm
S	22.5mm +/-0.4mm
LL	4mm +2mm
F	0.8mm +/-0.05mm

Packaging Specifications	
Packaging	Bulk, Bag
Packaging Quantity	396

General Information	
Series	R46 275 VAC
Dielectric	Metallized Polypropylene
Style	Radial
Features	EMI Safety
RoHS	Yes
Lead	Cut
Safety Class	X2
Qualifications	ENEC, UL, cUL, CQC
AEC-Q200	No
Typical Component Weight	6.463 g
Notes	We Recommended To Use R46 @ 310 VAC.

Specifications	
Capacitance	1 $\mu$ F
Capacitance Tolerance	20%
Voltage DC	560 VDC
Voltage AC	275 VAC (X2)
Temperature Range	-40/+110°C
Rated Temperature	110°C
Dissipation Factor	0.1% 1kHz
Insulation Resistance	30 GOhms
Max dV/dt	200 V/us