



Click [here](#) for the 3D model.

#### Dimensions

|    |                    |
|----|--------------------|
| L  | 18mm +0.3/-0.5mm   |
| H  | 17.5mm +0.1/-0.5mm |
| T  | 6mm +0.2/-0.5mm    |
| S  | 15mm +/-0.4mm      |
| LL | 25mm +2/-1mm       |
| F  | 0.6mm +/-0.05mm    |

#### Packaging Specifications

|                    |           |
|--------------------|-----------|
| Packaging          | Bulk, Bag |
| Packaging Quantity | 700       |

#### General Information

|                          |                          |
|--------------------------|--------------------------|
| Series                   | R46 275 VAC MINI         |
| Dielectric               | Metallized Polypropylene |
| Style                    | Radial                   |
| Features                 | EMI Safety               |
| RoHS                     | Yes                      |
| Termination              | Tinned Wire              |
| Lead                     | Wire Leads               |
| Safety Class             | X2                       |
| Qualifications           | ENEC, UL, cUL, CQC       |
| AEC-Q200                 | No                       |
| Typical Component Weight | 2.47 g                   |

#### Specifications

|                       |              |
|-----------------------|--------------|
| Capacitance           | 0.33 uF      |
| Capacitance Tolerance | 10%          |
| Voltage DC            | 560 VDC      |
| Voltage AC            | 275 VAC (X2) |
| Temperature Range     | -40/+110°C   |
| Rated Temperature     | 110°C        |
| Dissipation Factor    | 0.1% 1kHz    |
| Insulation Resistance | 100 GOhms    |
| Max dV/dt             | 400 V/us     |