

R46KI3330JHP2K

Aliases (46KI3330JHP2K)

R46 275 VAC MINI, Film, Metallized Polypropylene, Safety, 0.33 uF, 10%, 560 VDC, 275 VAC (X2), 110°C, 15mm



Click [here](#) for the 3D model.

Dimensions

| | |
|----|--------------------|
| L | 18mm +0.3/-0.5mm |
| H | 17.5mm +0.1/-0.5mm |
| T | 6mm +0.2/-0.5mm |
| S | 15mm +/-0.4mm |
| LL | 3.2mm +0.3/-0.2mm |
| F | 0.6mm +/-0.05mm |

Packaging Specifications

| | |
|--------------------|-----------|
| Packaging | Bulk, Bag |
| Packaging Quantity | 1000 |

General Information

| | |
|--------------------------|--------------------------|
| Series | R46 275 VAC MINI |
| Dielectric | Metallized Polypropylene |
| Style | Radial |
| Features | EMI Safety |
| RoHS | Yes |
| Termination | Cut (Tinned Wire) |
| Lead | Cut |
| Safety Class | X2 |
| Qualifications | ENEC, UL, cUL, CQC |
| AEC-Q200 | No |
| Typical Component Weight | 4.69 g |

Specifications

| | |
|-----------------------|--------------|
| Capacitance | 0.33 uF |
| Capacitance Tolerance | 10% |
| Voltage DC | 560 VDC |
| Voltage AC | 275 VAC (X2) |
| Temperature Range | -40/+110°C |
| Rated Temperature | 110°C |
| Dissipation Factor | 0.1% 1kHz |
| Insulation Resistance | 100 GOhms |
| Max dV/dt | 400 V/us |