



Click [here](#) for the 3D model.

Dimensions

| | |
|----|------------------|
| L | 32mm +0.3/-0.7mm |
| H | 33mm +0.1/-0.7mm |
| T | 18mm +0.2/-0.7mm |
| S | 27.5mm +/-0.4mm |
| LL | 4mm +2mm |
| F | 0.8mm +/-0.05mm |

Packaging Specifications

| | |
|--------------------|------|
| Packaging | Tray |
| Packaging Quantity | 256 |

General Information

| | |
|---------------|--|
| Series | R71 |
| Dielectric | Metallized Polypropylene |
| Style | Radial |
| Features | PFC and Pulse |
| RoHS | Yes |
| Termination | Cut (Tinned Wire) |
| Lead | Cut |
| AEC-Q200 | No |
| Miscellaneous | Above 105C DC And AC Voltage Derating Is 4%/C. |

Specifications

| | |
|-----------------------|---|
| Capacitance | 1.5 uF |
| Capacitance Tolerance | 5% |
| Voltage DC | 1000 VDC |
| Voltage AC | 275 VAC |
| Temperature Range | -40/+110°C |
| Rated Temperature | 105°C |
| Dissipation Factor | 0.1% 25C |
| Insulation Resistance | 20 GOhms |
| Max dV/dt | 180 V/us |
| ESR | 79.6 mOhms (100kHz) |
| Ripple Current | 2.11 Amps (100kHz 85C), 270 Amps (Peak) |
| Inductance | 18 nH |