



Click [here](#) for the 3D model.

Dimensions	
L	10mm +0.2mm
H	8mm +0.1mm
T	3mm +0.1mm
S	7.5mm +/-0.4mm
LL	17mm +1/-2mm
F	0.5mm +/-0.05mm

Packaging Specifications	
Packaging	Bulk
Packaging Quantity	1750

General Information	
Series	R66
Dielectric	Metallized Polyester Stacked
Style	Radial
Features	Automotive Grade, DC Multipurpose Applications
RoHS	Yes
Termination	Tinned Wire
Lead	Wire Leads
Qualifications	AEC-Q200
AEC-Q200	Yes
Typical Component Weight	0.41 g
Miscellaneous	Above 85C DC And AC Voltage Derating Is 1.25%/C.

Specifications	
Capacitance	0.47 uF
Capacitance Tolerance	5%
Voltage DC	63 VDC
Voltage AC	40 VAC
Temperature Range	-55/+105°C
Rated Temperature	85°C
Dissipation Factor	1% 1kHz, 1.5% 10kHz
Insulation Resistance	2.6596 GOhms
Max dV/dt	120 V/us
Inductance	8 nH