


R71VN41004030K

Aliases (71VN41004030K)

R71, Film, Metallized Polypropylene, General Purpose, 1uF, 10%, 520 VDC, 105°C, 22.5mm



Click [here](#) for the 3D model.

Dimensions

L	26.5mm +0.3/-0.5mm
H	18.5mm +0.1/-0.5mm
T	10mm +0.2/-0.5mm
S	22.5mm +/-0.4mm
LL	30mm +5mm
F	0.8mm +/-0.05mm

Packaging Specifications

Packaging	Bulk, Bag
Packaging Quantity	300

General Information

Series	R71
Dielectric	Metallized Polypropylene
Style	Radial
Features	PFC and Pulse
RoHS	Yes
Lead	Wire Leads
AEC-Q200	No
Typical Component Weight	6.449 g
Miscellaneous	Above 105C DC And AC Voltage Derating Is 4%/C.

Specifications

Capacitance	1uF
Capacitance Tolerance	10%
Voltage AC	250 VAC
Voltage DC	520 VDC
Temperature Range	-40/+110°C
Rated Temperature	105°C
Dissipation Factor	0.1% 25C
Insulation Resistance	30 GOhms
Max dV/dt	120 V/us
ESR	95.5 mOhms (100kHz)
Ripple Current	1.63 Amps (100kHz 85C), 120 Amps (Peak)
Inductance	18 nH