



Click [here](#) for the 3D model.

Dimensions

L	18mm +/-0.5mm
H	13.5mm +0.1/-0.5mm
T	7.5mm +0.2/-0.5mm
S	15mm +/-0.4mm
LL	30mm +5mm
F	0.6mm +/-0.05mm

Packaging Specifications

Packaging	Bulk, Bag
Packaging Quantity	700

General Information

Series	R71
Dielectric	Metallized Polypropylene
Style	Radial
Features	PFC and Pulse
RoHS	Yes
Termination	Tinned Wire
Lead	Wire Leads
AEC-Q200	No
Typical Component Weight	2.13 g
Miscellaneous	Above 105C DC And AC Voltage Derating Is 4%/C.

Specifications

Capacitance	0.47 uF
Capacitance Tolerance	10%
Voltage DC	420 VDC
Voltage AC	220 VAC
Temperature Range	-40/+110°C
Rated Temperature	105°C
Dissipation Factor	0.1% 25C
Insulation Resistance	63.8298 GOhms
Max dV/dt	160 V/us
ESR	118.5 mOhms (100kHz)
Ripple Current	1.21 Amps (100kHz 85C), 75.2 Amps (Peak)
Inductance	10 nH