

Aliases (71VR468050H6K)

R71H, Film, Metallized Polypropylene, Automotive Grade, 6.8 uF, 10%, 520 VDC, 85° C, 27.5 mm



Click here for the 3D model.

Dimensions	
L	32mm +0.3/-0.7mm
Н	28mm +0.1/-0.7mm
T	14mm +0.2/-0.7mm
S	27.5mm +/-0.4mm
LL	25mm +2/-1mm
F	0.8mm +/-0.05mm

Packaging Specifications		
Packaging	Tray	
Packaging Quantity	176	

General Information	
Series	R71H
Dielectric	Metallized Polypropylene
Style	Radial
Features	PFC and Pulse
RoHS	Yes
Termination	Tinned Wire
Lead	Wire Leads
Qualifications	AEC-Q200
AEC-Q200	Yes
Typical Component Weight	16.3 g
Miscellaneous	Above 105C DC And AC Voltage Derating Is 4%/C.

Specifications	
Capacitance	6.8 uF
Tolerance	10%
Voltage DC	520 VDC
Voltage AC	200 VAC
Temperature Range	-55/+125°C
Rated Temperature	85°C
Dissipation Factor	0.15% 25C
Insulation Resistance	4.4118 GOhms
Max dV/dt	70 V/us
ESR	9.362 mOhms (100kHz)
Ripple Current	9.05 Amps (100kHz 85C), 476 Amps (Peak)
Inductance	18 nH

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.


Generated 12/11/2025 © 2006 - 2025 YAGEO





Aliases (71VR468050H6K) R71H, Film, Metallized Polypropylene, Automotive Grade, 6.8 uF, 10%, 520 VDC, 85° C, 27.5 mm


Simulations


For the complete simulation environment please visit Y-SIM.
















Generated 12/11/2025 © 2006 - 2025 YAGEO



Aliases (71VR468050H6K) R71H, Film, Metallized Polypropylene, Automotive Grade, 6.8 uF, 10%, 520 VDC, 85°C, 27.5 mm





Generated 12/11/2025 © 2006 - 2025 YAGEO



Aliases (71VR468050H6K) R71H, Film, Metallized Polypropylene, Automotive Grade, 6.8 uF, 10%, 520 VDC, 85°C, 27.5 mm

These are simulations.

This is not a specification!

The responses shown represent the typical response for each part type. Specific responses may vary, depending on manufacturing variation affects of all parameters involved, including the specified tolerances applied to capacitance and unspecified variations of ESR, ESL, and leakage resistance.

The responses shown do not represent a specified or implied maximum capability of the device for all applications.

- The ESR used for ripple "Ripple Current/Voltage vs. Frequency" plots is the ESR at ambient temperature.

- The ESR in the "Temperature Rise vs. Ripple Current" plots is the ESR at ambient temperature. The ESR in the "Temperature Rise vs. Ripple Current" plots is adjusted to each incremental temperature rise before the power and ripple current is calculated. The effects shown herein are based on measured data from a multiple part sample of the parts in question. Ripple capability of this device will be factored by thermal resistance (Rth) created by circuit traces (addi affects of all parameters involved, including the specified tolerances applied to capacitance and unspecified variations of ESR, ESL, and leakage resistance.

 The peak voltages generated in the "Temperature Rise vs. Combined Ripple Currents" plot are calculated for each frequency and are not combined with voltages
- generated at any other harmonics.

 Please consult with the catalog or field applications engineer for maximum capability of the device in specific applications.

All product information and data (collectively, the "Information") are subject to change without notice.

KEMET K-SIM is designed to simulate behavior of components with respect to frequency, ambient temperature, and DC bias levels. The responses shown represent the typical response for each part type. Specific responses may vary, depending on manufacturing variation effects of all parameters involved, including the specified tolerances applied to capacitance and unspecified variations of ESR, ESL, and leakage resistance.

All Information given herein is believed to be accurate and reliable, but is presented without guarantee, warranty, or responsibility of any kind, expressed or implied. Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute – and we specifically disclaim – any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

If you have any questions please contact K-SIM.

Generated 12/11/2025 © 2006 - 2025 YAGEO