


R75IW515050H4J

Aliases (75IW515050H4J)

R75H, Film, Metallized Polypropylene, Automotive Grade, 15 uF, 5%, 250 VDC, 105°C, 37.5mm



Click [here](#) for the 3D model.

Dimensions

L	41.5mm +0.3/-0.7mm
H	40mm +0.1/-0.7mm
T	20mm +0.3/-0.7mm
S	37.5mm +/-0.4mm
LL	25mm +2/-1mm
F	1mm +/-0.05mm

Packaging Specifications

Packaging	Bulk, Bag
Packaging Quantity	84

General Information

Series	R75H
Dielectric	Metallized Polypropylene
Style	Radial
Features	Automotive Grade, Pulse
RoHS	Yes
Lead	Wire Leads
Qualifications	AEC-Q200
AEC-Q200	Yes
Typical Component Weight	36.4 g
Miscellaneous	Above 105C DC And AC Voltage Derating Is 1.25%/C.

Specifications

Capacitance	15 uF
Capacitance Tolerance	5%
Voltage AC	160 VAC
Voltage DC	250 VDC
Temperature Range	-55/+125°C
Rated Temperature	105°C
Dissipation Factor	0.1% 1kHz
Insulation Resistance	2 GOhms
Max dV/dt	40 V/us
ESR	3.18 mOhms (100kHz)
Ripple Current	18.3 Amps (100kHz 90C), 600 Amps (Peak)
Inductance	20 nH