


R75QW368050L0J

Aliases (75QW368050L0J)

R75, Film, Metallized Polypropylene, General Purpose, 0.68 uF, 5%, 1,000 VDC, 85°C, 37.5 mm



Click here for the 3D model.		
Dimensions		
L	41.5mm +0.3/-0.7mm	
Н	15mm +0.1/-0.7mm	
Т	24mm +0.3/-0.7mm	
S	37.5mm +/-0.4mm	
LL	25mm +2/-1mm	
F	1mm +/-0.05mm	

Packaging Specifications		
Packaging	Tray	
Packaging Quantity	108	

General Information	
Series	R75
Dielectric	Metallized Polypropylene
Style	Radial
Features	Pulse
RoHS	Yes
Termination	Tinned Wire
Lead	Wire Leads
AEC-Q200	No
Typical Component Weight	15.7 g
Miscellaneous	Above 85C DC voltage derating is 2%/C and AC voltage derating is 1.25%/C .

Specifications	
Capacitance	0.68 uF
Tolerance	5%
Voltage DC	1000 VDC
Voltage AC	300 VAC
Temperature Range	-55/+105°C
Rated Temperature	85°C
Dissipation Factor	0.05% 1kHz, 0.08% 10kHz
Insulation Resistance	44.1176 GOhms
Max dV/dt	200 V/us
ESR	9.362 mOhms (100kHz)
Ripple Current	9.36 Amps (100kHz 85C), 136 Amps (Peak)
Inductance	20 nH

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 12/03/2025 © 2006 - 2025 YAGEO