

## R75RW4100AA30J

Aliases (75RW4100AA30J)

R75, Film, Metallized Polypropylene, General Purpose, 1 uF, 5%, 1250 VDC, 85°C, 37.5mm



Click [here](#) for the 3D model.

### Dimensions

L	41.5mm +0.3/-0.7mm
H	40mm +0.1/-0.7mm
T	20mm +0.3/-0.7mm
S	37.5mm +/-0.4mm
LL	4mm +2mm
F	1mm +/-0.05mm

### Packaging Specifications

Packaging	Tray
Packaging Quantity	126

### General Information

Series	R75
Dielectric	Metallized Polypropylene
Style	Radial
Features	Pulse
RoHS	Yes
Termination	Cut (Tinned Wire)
Lead	Cut
AEC-Q200	No
Typical Component Weight	36.1 g
Miscellaneous	Above 85C DC And AC Voltage Derating Is 1.25%/C.

### Specifications

Capacitance	1 uF
Capacitance Tolerance	5%
Voltage DC	1250 VDC
Voltage AC	600 VAC
Temperature Range	-55/+105°C
Rated Temperature	85°C
Dissipation Factor	0.05% 1kHz, 0.08% 10kHz
Insulation Resistance	30 GOhms
Max dV/dt	360 V/us
ESR	3.2 mOhms (100kHz)
Ripple Current	18.3 Amps (100kHz 85C), 550 Amps (Peak)
Inductance	20 nH