

## R75RW418050H2J

Aliases (75RW418050H2J)

R75H, Film, Metallized Polypropylene, Automotive Grade, 1.8 uF, 5%, 1250 VDC, 105°C, 37.5mm



Click [here](#) for the 3D model.

### Dimensions

L	41.5mm +0.3/-0.7mm
H	45mm +0.1/-0.7mm
T	30mm +0.3/-0.7mm
S	37.5mm +/-0.4mm
LL	25mm +2/-1mm
F	1mm +/-0.05mm

### Packaging Specifications

Packaging	Bulk, Bag
Packaging Quantity	60

### General Information

Series	R75H
Dielectric	Metallized Polypropylene
Style	Radial
Features	Automotive Grade, Pulse
RoHS	Yes
Lead	Wire Leads
Qualifications	AEC-Q200
AEC-Q200	Yes
Typical Component Weight	61.9 g
Miscellaneous	Above 105C DC And AC Voltage Derating Is 1.25%/C.

### Specifications

Capacitance	1.8 uF
Capacitance Tolerance	5%
Voltage DC	1250 VDC
Voltage AC	600 VAC
Temperature Range	-55/+125°C
Rated Temperature	105°C
Dissipation Factor	0.06% 1kHz
Insulation Resistance	16.6667 GOhms
Max dV/dt	550 V/us
ESR	2.653 mOhms (100kHz)
Ripple Current	21.69 Amps (100kHz 90C), 990 Amps (Peak)
Inductance	20 nH