



Click [here](#) for the 3D model.

Dimensions	
L	32mm +0.3/-0.7mm
H	20mm +0.1/-0.7mm
T	11mm +0.2/-0.7mm
S	27.5mm +/-0.4mm
LL	25mm +2/-1mm
F	0.8mm +/-0.05mm

Packaging Specifications	
Packaging	Bulk, Bag
Packaging Quantity	336

General Information	
Series	R75H
Dielectric	Metallized Polypropylene
Style	Radial
Features	Automotive Grade, Pulse
RoHS	Yes
Lead	Wire Leads
Qualifications	AEC-Q200
AEC-Q200	Yes
Typical Component Weight	7.8 g
Miscellaneous	Above 105C DC And AC Voltage Derating Is 1.25%/C.

Specifications	
Capacitance	0.1 uF
Capacitance Tolerance	5%
Voltage AC	650 VAC
Voltage DC	1600 VDC
Temperature Range	-55/+125°C
Rated Temperature	105°C
Dissipation Factor	0.04% 1kHz, 0.06% 10kHz, 0.25% 100kHz
Insulation Resistance	100 GOhms
Max dV/dt	1500 V/us
ESR	31.8 mOhms (100kHz)
Ripple Current	7.56 Amps (100kHz 90C), 150 Amps (Peak)
Inductance	18 nH