


## R75TW382050H3J

Aliases (75TW382050H3J) R75H, Film, Metallized Polypropylene, Automotive Grade, 0.82 uF, 5%, 1,600 VDC, 105°C, 37.5 mm



Click here for the 3D model.

Dimensions	
L	41.5mm +0.3/-0.7mm
Н	40mm +0.1/-0.7mm
Т	20mm +0.3/-0.7mm
S	37.5mm +/-0.4mm
LL	25mm +2/-1mm
F	1mm +/-0.05mm

Packaging Specifications		
Packaging	Bulk, Bag	
Packaging Quantity	84	

General Information	
Series	R75H
Dielectric	Metallized Polypropylene
Style	Radial
Features	Automotive Grade, Pulse
RoHS	Yes
Termination	Tinned Wire
Lead	Wire Leads
Qualifications	AEC-Q200
AEC-Q200	Yes
Typical Component Weight	39.7 g
Miscellaneous	Above 105C DC And AC Voltage Derating Is 1.25%/C.

Specifications	
Capacitance	0.82 uF
Tolerance	5%
Voltage DC	1600 VDC
Voltage AC	650 VAC
Temperature Range	-55/+125°C
Rated Temperature	105°C
Dissipation Factor	0.05% 1kHz, 0.08% 10kHz
Insulation Resistance	36.5854 GOhms
Max dV/dt	750 V/us
ESR	3.9 mOhms (100kHz)
Ripple Current	16.57 Amps (100kHz 90C), 615 Amps (Peak)
Inductance	20 nH

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute – and we specifically disclaim – any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 11/23/2025 © 2006 - 2025 YAGEO