


R79PC1220AA40J

Aliases (79PC1220AA40J)

Not for New Design

R79, Film, Metallized Polypropylene, General Purpose, 2200 pF, 5%, 630 VDC, 85°C, 5mm



Click [here](#) for the 3D model.

General Information

| | |
|---------------|--|
| Series | R79 |
| Dielectric | Metallized Polypropylene |
| Style | Radial |
| Features | Pulse |
| RoHS | Yes |
| Termination | Cut (Tinned Wire) |
| Lead | Cut |
| AEC-Q200 | No |
| Miscellaneous | Above 85C DC And AC Voltage Derating Is 1.25%/C. |
| Notes | Series Replaced by R75. |

Specifications

| | |
|-----------------------|-------------------------------------|
| Capacitance | 2200 pF |
| Capacitance Tolerance | 5% |
| Voltage DC | 630 VDC |
| Voltage AC | 220 VAC |
| Temperature Range | -55/+105°C |
| Rated Temperature | 85°C |
| Dissipation Factor | 0.06% 1kHz, 0.1% 10kHz, 0.3% 100kHz |
| Insulation Resistance | 100 GOhms |
| Max dV/dt | 500 V/us |
| Inductance | 6 nH |

Dimensions

| | |
|----|-------------------|
| L | 7.2mm +0.2/-0.5mm |
| H | 7.5mm +0.1/-0.5mm |
| T | 3.5mm +0.1/-0.5mm |
| S | 5mm +/-0.4mm |
| LL | 4mm +2mm |
| F | 0.5mm +/-0.05mm |

Packaging Specifications

| | |
|--------------------|-----------|
| Packaging | Bulk, Bag |
| Packaging Quantity | 2000 |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.