



Click [here](#) for the 3D model.

General Information

Series	RG
Style	Metal Cylinder
Description	Noise Filters
RoHS	With Exemptions
Qualifications	UL, TUV
AEC-Q200	No
Miscellaneous	55 K Self-Temperature Rise Max.
Lead	Fast On
Terminal Type	Faston

Dimensions

D	50mm NOM
L	60mm NOM
L1	12mm NOM
Lead	Fast On

Packaging Specifications

Packaging	Tray, Box
Packaging Quantity	25
Typical Component Weight	220 g

Specifications

Voltage AC	250 VAC
Voltage	1500 VAC Withstanding Voltage 1 Min. Line to Ground
Rated Current	8 A (AC/DC)
Ripple Current	8 A (AC/DC)
Temperature Range	-25/+55°C
Leakage Current	1 mA
ESR	100 MOhms MIN Insulation 500 VDC 1 Min. Line To Ground

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.