



Click [here](#) for the 3D model.

Dimensions

D	12mm MAX
L	15mm MAX
S	8.5mm NOM
F	0.4mm NOM

Packaging Specifications

Typical Component Weight	5.769 g
Packaging	Bulk
Packaging Quantity	1600

General Information

Series	SBC6
Style	Through-Hole Drum
Core	Ferrite
Description	Radial Leaded, Ferrite Power Inductors
Features	DC-DC Converters, Nickel-Zinc (NiZn) Ferrite Core
RoHS	Yes
Lead	Wire Leads
Miscellaneous	Soft Lead Terminal

Specifications

Inductance	330 uH
Inductance Tolerance	10%
Temperature Range	-20/+105°C
Shielded	false
Current	0.87 Amps
DC Resistance	0.41 Ohms