



Click [here](#) for the 3D model.

General Information

Series	SBCP-80HY
Style	Through-Hole Drum
Core	Ferrite
Description	Radial Leaded, Ferrite Power Inductors
Features	DC-DC Converters, Nickel-Zinc (NiZn) Ferrite Core
RoHS	Yes
Lead	Wire Leads

Dimensions

D	9.5mm MAX
L	11mm MAX
S	5mm +/-0.5mm
F	0.6mm NOM

Packaging Specifications

Typical Component Weight	2.27 g
Packaging	Bulk
Packaging Quantity	4000

Specifications

Inductance	10000 uH (0.01 MHz)
Inductance Tolerance	10%
Inductance	0.01 H
Temperature Range	-20/+105°C
Shielded	false
Current	0.1 Amps
DC Resistance	19.1 Ohms
DC Resistance	19.1 Ohms