


SBCP-80HY103HB

Aliases (UPI080HY103HB0)

KEMET, SBCP-80HY, Ferrite, 10%, 0.01H, 9.5mm, 5mm



Click [here](#) for the 3D model.

Dimensions

D	9.5mm MAX
L	11mm MAX
S	5mm +/-0.5mm
F	0.6mm NOM

Packaging Specifications

Typical Component Weight	2.27 g
Packaging	Bulk
Packaging Quantity	4000

General Information

Series	SBCP-80HY
Style	Through-Hole Drum
Core	Ferrite
Description	Radial Leaded, Ferrite Power Inductors
Features	DC-DC Converters, Nickel-Zinc (NiZn) Ferrite Core
RoHS	Yes
Lead	Wire Leads

Specifications

Inductance	0.01H
Inductance Tolerance	10%
Temperature Range	-20/+105°C
Shielded	No
Current	0.1 Amps
DC Resistance	19.1 Ohms