


[Click here for the 3D model.](#)
General Information

Series	SBCP-80HY
Style	Through-Hole Drum
Core	Ferrite
Description	Radial Leaded, Ferrite Power Inductors
Features	DC-DC Converters, Nickel-Zinc (NiZn) Ferrite Core
RoHS	Yes
Lead	Wire Leads
Notes	Contains 4 Reels of 500 pieces each.

Dimensions

D	9.5mm MAX
L	11mm MAX
S	5mm +/-0.5mm
F	0.6mm NOM

Specifications

Inductance	47 uH (0.01 MHz)
Inductance Tolerance	10%
Rated Current	1.9 Amps
Temperature Range	-20/+105°C
Shielded	No
DC Resistance	130 mOhms
DC Resistance	0.13 Ohms

Packaging Specifications

Typical Component Weight	1.955 g
Packaging	Ammo
Packaging Quantity	2000

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.