


**General Information**

Series	SC-D
Style	Through-Hole
RoHS	Yes
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Temperature Rise Maximum: 45 K.
Core	Ni-Zn Ferrite

 Click [here](#) for the 3D model.

**Dimensions**

D	34mm MAX
H	23mm MAX
LL	15mm +/-2mm
S	22mm
S1	21mm
Wire Size	1mm

**Specifications**

Voltage AC	250 VAC
Inductance	60 uH
Rated Current	8 A
Temperature Range	-40/+105°C
DC Resistance	30 mOhms

**Packaging Specifications**

Packaging	Tray
Packaging Quantity	200
Typical Component Weight	30 g

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.