


## SC-09-E075JH

Aliases (UALSC09E075JH0)

Common Mode Chokes - Power, KEMET, SC-JH, Through-Hole, Common Mode, 750 uH



General Information	
Series	SC-JH
Style	Through-Hole
RoHS	Yes
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Temperature Rise Maximum: 60 K.
Core	Mn-Zn Ferrite

## Click here for the 3D model.

Dimensions	
D	24mm MAX
Т	24.5mm MAX
Н	15mm MAX
LL	3.5mm +/-1mm
S	12mm NOM
S1	20mm NOM
Wire Size	1.1mm

Packaging Specifications		
Packaging	Tray	
Packaging Quantity	250	
Typical Component Weight	13 g	

Specifications	
Voltage AC	250 VAC
Inductance	0.75 mH
Rated Current	9 A
Temperature Range	-40/+120°C
DC Resistance	9 mOhms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 11/22/2025 © 2006 - 2025 YAGEO