



Click [here](#) for the 3D model.

#### Dimensions

|           |              |
|-----------|--------------|
| D         | 32mm MAX     |
| T         | 34mm MAX     |
| H         | 18mm MAX     |
| LL        | 3.5mm +/-1mm |
| S         | 11mm NOM     |
| S1        | 28mm NOM     |
| Wire Size | 0.8mm        |

#### Packaging Specifications

|                          |        |
|--------------------------|--------|
| Packaging                | Tray   |
| Packaging Quantity       | 180    |
| Typical Component Weight | 27.2 g |

#### General Information

|               |   |
|---------------|---|
| Series        | SC_JKH                                      |
| Style         | Through-Hole                                |
| RoHS          | Yes   |
| Notes         | Lead Spacing (S/S1) Are For Reference Only. |
| Miscellaneous | Temperature Rise Maximum: 80 K.             |
| Core          | Mn-Zn Ferrite                               |

#### Specifications

|                   |             |
|-------------------|-------------|
| Voltage AC        | 250 VAC     |
| Inductance        | 8.1mH       |
| Current           | 5 A         |
| Temperature Range | -25/+120°C  |
| DC Resistance     | 72.45 mOhms |