



Click [here](#) for the 3D model.

Dimensions

D	16mm MAX
T	12mm MAX
H	16mm MAX
LL	3.1mm +/-0.5mm
S	6mm NOM
S1	10mm NOM
Wire Size	0.45mm

Packaging Specifications

Packaging	Tray
Packaging Quantity	1080
Typical Component Weight	5 g

General Information

Series	SCF-J/JH
Style	Through-Hole
Features	High Impedance, Space Saving
RoHS	Yes
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Temperature Rise Maximum: 70 K.
Core	Nanocrystal

Specifications

Voltage AC	250 VAC
Inductance	11.9 mH (10 kHz)
Current	2.5 A
Temperature Range	-40/+120°C
DC Resistance	82.6 mOhms