


SCF-02-350JH

Aliases (UALSCF02350JH0)

Common Mode Chokes - Power, KEMET, SCF-J/JH, Through-Hole, Common Mode, 0.035 H



Click [here](#) for the 3D model.

General Information

Series	SCF-J/JH
Style	Through-Hole
Features	High Impedance, Space Saving
RoHS	Yes
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Temperature Rise Maximum: 45 K.
Core	Nanocrystal

Dimensions

D	16mm MAX
T	15mm MAX
H	15.5mm MAX
LL	3mm +/-0.5mm
S	5.08mm NOM
S1	7.62mm NOM
Wire Size	0.4mm

Packaging Specifications

Packaging	Tray
Packaging Quantity	600
Typical Component Weight	5.4 g

Specifications

Voltage AC	250 VAC
Inductance	35 mH
Rated Current	2 A
Temperature Range	-40/+120°C
DC Resistance	220 mOhms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.