



Click [here](#) for the 3D model.

Dimensions

D	15mm MAX
T	14mm MAX
H	15mm MAX
LL	3.5mm +/-1mm
S	5mm NOM
S1	10mm NOM
Wire Size	0.5mm

Packaging Specifications

Packaging	Tray
Packaging Quantity	360
Typical Component Weight	4 g

General Information

Series	SCF-J/JH
Style	Through-Hole
Features	High Impedance, Space Saving
RoHS	Yes
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Temperature Rise Maximum: 55 K.
Core	Nanocrystal

Specifications

Voltage AC	250 VAC
Inductance	6.5 mH (10 kHz)
Current	3 A
Temperature Range	-40/+120°C
DC Resistance	70 mOhms