



Click [here](#) for the 3D model.

### Dimensions

|           |                  |
|-----------|------------------|
| D         | 40.5mm MAX       |
| T         | 37.2mm MAX       |
| H         | 20.9mm +1/-0.6mm |
| LL        | 3.5mm +/-0.5mm   |
| S         | 22.5mm +/-0.5mm  |
| S1        | 28.5mm +/-0.5mm  |
| Wire Size | 1.6mm            |
| BD        | 30.2mm +/-0.5mm  |
| BT        | 36.70mm +/-0.5mm |

### Packaging Specifications

|                          |        |
|--------------------------|--------|
| Packaging                | Tray   |
| Packaging Quantity       | 80     |
| Typical Component Weight | 50.2 g |

### General Information

|                |   |
|----------------|---|
| Series         | SC29XV                                      |
| Style          | Through-Hole                                |
| Features       | High Rated Voltage                          |
| RoHS           | Yes   |
| Qualifications | AEC-Q200                                    |
| Notes          | Lead Spacing (S/S1) Are For Reference Only. |
| Miscellaneous  | Temperature Rise Maximum: 35 K.             |
| Core           | Nanocrystal                                 |

### Specifications

|                   |            |
|-------------------|------------|
| Voltage AC        | 1000 VAC   |
| Voltage DC        | 1000 VDC   |
| Inductance        | 3.2 mH     |
| Current           | 12 A       |
| Temperature Range | -40/+150°C |
| DC Resistance     | 6.45 mOhms |