


SCF25XV-350-2R4A003JV

Aliases (UALCF250003JV0) Common Mode Chokes - Power, KEMET, SC25XV, Through-Hole, Common Mode, 220 uH



General Information	
Series	SC25XV
Style	Through-Hole
Features	High Rated Voltage
RoHS	Yes
Qualifications	AEC-Q200
AEC-Q200	Yes
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Temperature Rise Maximum: 45 K.
Core	Nanocrystal

Click here for the 3D model.

Dimensions	
D	37.5mm MAX
T	26mm MAX
Н	32.5mm +1/-0.6mm
LL	3.5mm +/-0.5mm
S	20.5mm +/-0.5mm
S1	18.5mm +/-0.5mm
Wire Size	2.4mm
BD	28.2mm +/-0.5mm
BT	25.50mm +/-0.5mm

Voltage AC	1000 VAC	
Voltage DC	1000 VDC	
Inductance	0.22 mH	
Rated Current	35 A	
Temperature Range	-40/+150°C	
DC Resistance	0.65 mOhms	

Specifications

Packaging Specifications	
Packaging	Tray
Packaging Quantity	140
Typical Component Weight	44.3 g

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 11/04/2025 © 2006 - 2025 YAGEO