



Click [here](#) for the 3D model.

#### General Information

Series	SC39XV-Y
Style	Through-Hole
Features	High Rated Voltage
RoHS	Yes
Qualifications	AEC-Q200
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Temperature Rise Maximum: 50 K.
Core	Nanocrystal

#### Dimensions

D	53mm MAX
H	31mm +1/-0.6mm
LL	4.5mm +/-0.5mm
Wire Size	1.8mm
BD	51mm +/-0.5mm
BT	50mm +/-0.5mm

#### Packaging Specifications

Packaging	Tray
Packaging Quantity	48
Typical Component Weight	118.9 g

#### Specifications

Voltage AC	1000 VAC
Voltage DC	1000 VDC
Inductance	0.9 mH (100 kHz)
Inductance Tolerance	-30/+50%
Current	17 A
Temperature Range	-40/+150°C
DC Resistance	2.83 mOhms